



DATENBLATT

JETFLEX[®] CBD 105

COARSE BUBBLE DIFFUSER


JETFLEX[®] CBD 105 COARSE BUBBLE DIFFUSER

Membrane material

Silicone


Diffuser body

Reinforced Polypropylene (PP-GF) with R ¾" external tapered thread



Dimensions

Overall Diameter	Total Height	Threaded Length	Membrane Thickness
105 mm	45 mm	25 mm	2 mm



Installation

You may install CBD 105 using our rubber saddle (EPDM) or our plastic saddle clamp. Please see our brochure "Accessories" for details and further alternatives.

Performance data

Airflow	Headloss	SSOTE
Minimum: 2 m ³ /h (33 liters/minute) @ STP	10 hPa	2 %/m
Maximum: 25 m ³ /h (420 liters/minute) @ STP	40 hPa	1 %/m

Coarse bubble diffusers are mainly used through mixing capabilities. The rising air induces a strong current, thus removing sludge from the bottom of the tank. They are therefore a very good alternative for many mechanical aeration systems.

JETFLEX[®] CBD 105 COARSE BUBBLE DIFFUSER

CONTACT

Tel +49 511 - 646 44 0

Fax +49 511 - 646 44 499

www.jaeger-envirotech.com

info@jaeger-envirotech.com



Jaeger EnviroTech GmbH

Lohweg 1

30559 Hannover

Disclaimer

We exclude any liability for the information and product presentations provided. For contents of a technical nature, these are based on the status of their publication. Existing copyrights and rights to names remain unaffected.